# EURO YSER

## **TECHNICAL DATA SHEET**

YT 311

## **PRODUCT DESCRIPTION**

YT 311 is a glycerol ester of gum rosin, which has been stabilised to provide excellent thermal resistance and excellent resistance against oxidation.

#### **CHARACTERISTICS**

Light yellow solid.

Is compatible with all the usual compounds as:

- EVA polymers, SIS, SBS, SBR, natural rubber, butyl rubber, neoprene, and other polymers;
- Hydrocarbon and terpene resins.

Is soluble in:

- Aromatic and aliphatic hydrocarbon solvents;
- Esters and Ketones.

Is insoluble in:

- Alcohol and water.

## PRODUCT SPECIFICATIONS<sup>1</sup>

	Product Specification	Typical Properties	Units
Acid Number	15 max	10	mg KOH/g
Softening Point (R&B)	86 - 90	88	°C
Colour Gardner (50%, Toluene)	4 max	3	

#### **REGULATORY STATUS**

Meets the requirements of the Code of Federal Regulation, Title 21, under the following sections:

- 175.105 Adhesives.

## **APPLICATIONS**

It is specially recommended for use as tackifier in Pressure Sensitive Adhesives (P.S.A.) due to its:

- Excellent thermal resistance;
- Good compatibility with waxes;
- Total compatibility with most polymers;
- Excellent tack;
- Excellent resistance oxidation due to low abietic acid contents.

It can also be used in EVA hot melts, rubber compounding and other application.

## FORM OF SUPPLY

Flakes in 25 Kg bags on pallet 1000 kg weight;

in 1000 kg big-bag.

Pearls in 25 Kg bags on pallet 1000 kg weight;

in 1000 kg big-bag.

Block Metallic drums of 250 Kg on pallets 1000 Kg weight.

## SHELF LIVE

Up to six months under normal storage conditions.

The information in this Technical Data Sheet is, to the best of our knowledge, true and accurate, but since the conditions of use are beyond our control, no warranty is given or to be implied in respect of such information. We are, at all times, willing to study customer's specific outlets involving our products in order to enable their most effective use.

EURO - YSER, Produtos Químicos, S.A.

15 - 03 - 2017

<sup>&</sup>lt;sup>1</sup>Analytical Methods are available on request